
E10564

Female cordset

ADOAH042MSS0002B03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...30 DC
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 67
Mechanical data		
Dimensions	[mm]	29 x 15 x 44
Material		PA 6.6
Molded-body material		PA 6.6
Material nut		aluminum
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
Remarks		
Pack quantity		1 pcs.

E10564

Female cordset

ADOAH042MSS0002B03

Electrical connection


Cable: 2 m, PUR, orange, Ø 4.5 mm; 3 x 0.34 mm²

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: PA 6.6; Locking: aluminum



Connection



	Core colors :
BN =	brown
BK =	black
BU =	blue