
# E10940

## Connection cable

VDOAH042MSS00,6H03STGF030MSS

Article no longer available - archive entry


Alternative articles: E11347
When selecting an alternative article and accessories please note that technical data may differ!




| | | |
|---|---|---|
| **Application** | | |
| System | | Halogen-free |
| **Electrical data** | | |
| Operating voltage | [V] | 10...30 DC |
| Protection class | | III |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...90 |
| Protection | | IP 67 |
| **Mechanical data** | | |
| Material | | TPU (urethane) |
| Molded-body material | | TPU (urethane) |
| Material nut | | brass, nickel-plated |
| **Displays / operating elements** | | |
| Display | Switching status | 1 x LED, yellow |
| | Power | 1 x LED, green |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |

**Electrical connection - plug**

Connector: 1 x M8, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated



# E10940


## Connection cable

VDOAH042MSS00,6H03STGF030MSS

### Electrical connection

Cable: 0.6 m, TPU (urethane), Halogen-free; 3 x 0.34 mm² (42 x Ø 0.1 mm )

Connection




### Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated

