
E10947

Female cordset

ADOAK190MSS0005B19

Article no longer available - archive entry




Electrical data		
Operating voltage	[V]	10...30 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 65
Mechanical data		
Dimensions	[mm]	51 x 26 x 58
Material		brass nickel-plated
Molded-body material		brass, nickel-plated
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 5 m, PUR, black, Ø 11 mm; 16 x 0.5 mm² (64 x Ø 0.1 mm) + 3 x 1.0 mm² (128 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M23; Moulded body: brass, nickel-plated; Locking: brass, nickel-plated




E10947

Female cordset

ADOAK190MSS0005B19

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
RD =	red
VT =	lilac
WH =	white
YE =	yellow