
E10110

Male receptacle

ESTGB040MSS00,3E03 (PG13,5)

Article no longer available - archive entry



1 O-ring

Application		
System		gold-plated contacts
Electrical data		
Operating voltage	[V]	< 600 AC/DC
Operating conditions		
Ambient temperature	[°C]	-20...100
Protection		IP 68
Mechanical data		
Weight	[g]	45.5
Mounting thread		1/2" NPT
Material		aluminum anodized
Molded-body material		aluminum, anodized
Remarks		
Pack quantity		1 pcs.

E10110

Male receptacle

ESTGB040MSS00,3E03 (PG13,5)

Electrical connection


, PVC; 4 x 0.34 mm² / AWG 22

Electrical connection - plug

Connector: 1 x 7/8", straight; coding: A; Moulded body: aluminum, anodized; Contacts: gold-plated



Connection



	Core colors :
BK =	black
GN =	green
RD =	red
WH =	white