E10158


Female cordset

ADOAH042MSS0002E03

Article no longer available - archive entry

Alternative articles: EVC615

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data			
Operating voltage	[V]		10...30 DC
Outputs			
Electrical design			PNP
Operating conditions			
Ambient temperature	[°C]		-25...80
Protection			IP 67
Mechanical data			
Weight	[g]		65.4
Dimensions	[mm]		26 x 15 x 38
Material			TPU (urethane) transparent
Molded-body material			TPU (urethane), transparent
Material nut			brass, nickel-plated
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10158

Female cordset

ADOAH042MSS0002E03

Electrical connection


Cable: 2 m, PUR, black, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane), transparent; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm



Connection



	Core colors :
BN =	brown
BK =	black
BU =	blue