
E10289

Female cordset

ADOAG032--S0010A03

Article no longer available - archive entry



Application			
System			Halogen-free
Electrical data			
Operating voltage	[V]		10...30 DC
Protection class			III
Outputs			
Electrical design			PNP
Operating conditions			
Ambient temperature	[°C]		-25...90
Protection			IP 65
Mechanical data			
Material			TPU (urethane) transparent
Molded-body material			TPU (urethane), transparent
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10289

Female cordset


ADOAG032--S0010A03

Electrical connection


Cable: 10 m, PUR, Halogen-free, black, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - Socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU (urethane), transparent; Locking: Snap-in



Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue