
E11462

Connection cable

VDOAH043MSS00,6H04STGH040MSS

Article no longer available - archive entry



Application			
System		Free from silicone; Halogen-free; gold-plated contacts	
Free from silicone		yes	
Electrical data			
Operating voltage	[V]	10...30 DC	
Max. current load total	[A]	3	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...85	
Protection		IP 68	
Mechanical data			
Material		PUR	
Molded-body material		PUR	
Material nut		brass, nickel-plated	
Displays / operating elements			
Display		Switching status	2 x LED, yellow
		Power	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

E11462

Connection cable

VDOAH043MSS00,6H04STGH040MSS

Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm



Electrical connection

Cable: 0.6 m, PUR, Halogen-free, black, Ø 4.7 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm

