
E20631

Fiber optic diffuse reflection sensor

FT-11-E-A-M6/F2X1/0,6M

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Monitoring range		
Range with fiber optic amplifier type		OBF
OBF		
Range fiber optics	[mm]	70
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Version of sensing head		straight
Sensing head thread		M6
Sensing head length	[mm]	35
Total length	[mm]	600
Min. bending radius	[mm]	30
Fiber material		PMMA
Fiber head material		aluminum
Fiber sheath material		PE

E20631

Fiber optic diffuse reflection sensor

FT-11-E-A-M6/F2X1/0,6M

Accessories	
Accessories (optional)	Cutter for fibers:, E20600

Remarks	
Pack quantity	1 pcs.