E20149


Fiber optic diffuse reflection sensor

FT-00-P-A-E3/0,8M

Article no longer available - archive entry

Alternative articles: E20123

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Diffuse reflection sensor
Monitoring range		
Range with fiber optic amplifier type		OKF; OUF
OKF		
Range fiber optics	[mm]	40
OUF		
Range fiber optics	[mm]	40
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Version of sensing head		straight
Sensing head diameter	[mm]	3
Sensing head length	[mm]	25
Total length	[mm]	800

E20149

Fiber optic diffuse reflection sensor

FT-00-P-A-E3/0,8M

Min. bending radius	[mm]	20
Material		Adapter: PPE
Fiber material		glass
Fiber head material		aluminum
Fiber sheath material		PVC
Remarks		
Pack quantity		1 pcs.