E20246

Fiber optic diffuse reflection sensor

FT-30-A-A-M8/4M

Article no longer available - archive entry

Alternative articles: E20152

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Diffuse reflection sensor
Monitoring range		
Range with fiber optic amplifier type		OIF
OIF		
Range fiber optics	[mm]	36
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		angled
Sensing head thread		M8
Total length	[mm]	4000
Min. bending radius	[mm]	30
Material		Adapter: PA
Fiber material		glass
Fiber head material		aluminum

E20246

Fiber optic diffuse reflection sensor

FT-30-A-A-M8/4M

Fiber sheath material	aluminum

Remarks	
Pack quantity	1 pcs.