E70125

Connection cable

VDOGH040PL-0005A03STGH040MSS

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...36 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	15 x 15 x 42
Material		TPU (urethane); PBT
Molded-body material		TPU / PBT
Material nut		PBT / PA
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU / PBT; Locking: PBT

E70125

Connection cable

VDOGH040PL-0005A03STGH040MSS

Electrical connection

Cable: 5 m, PUR / PVC; 4 x 0.25 mm²

Connection



Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU / PBT; Locking: PA