
E80409

RFID tag

ID-TAG/86 x 54 /04



Electrical data		
Operating frequency	[MHz]	860...960
Memory size	[bit]	192
Memory type		EEPROM
Chip type		Impinj Monza 4QT
Electronic product code (EPC)		96-128 Bits; (User: 32-64 Bits)
RFID standard		EPC Class1 GEN2/ISO 18000-6C
Max. read cycles		unlimited
Max. write cycles		100000
Operating conditions		
Ambient temperature	[°C]	-35...50
Mechanical data		
Weight	[g]	49
Dimensions	[mm]	54 x 85.6 x 0.76
Material		housing: PVC
Remarks		
Pack quantity		10 pcs.
Other data		

read distance (m)

DTE80x	1.8
DTE90x	1.1
ANT860 / ANT960	4.8
ANT820 / ANT920	1.5