
JAT201

Diffuse reflection sensor

AFK3050BBPKG/M/V4A/US-104



Product characteristics			
Dimensions	[mm]	M12 x 1 / L = 63	
Operating conditions			
Ambient temperature	[°C]	0...100	
Protection		IP 65; IP 67; IP 68; IP 69K	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m (80...1000 MHz)
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-5 Surge	0,5 kV
		EN 61000-4-6 HF conducted	10 V (0,15...80 MHz)
		EN 55011	class B
MTTF	[years]	1048	
Mechanical data			
Weight	[g]	84.5	
Dimensions	[mm]	M12 x 1 / L = 63	
Thread designation		M12 x 1	
Remarks			
Pack quantity		1 pcs.	

Electrical connection - plug

Connector: 1 x M12; coding: A

