E20524


Fibre optic diffuse reflection sensor

FT-00-M-V-M6/2m

Article no longer available - archive entry

Alternative articles: E20570

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF; OUF
OKF		
Range fibre optics	[mm]	32
OUF		
Range fibre optics	[mm]	32
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Version of sensing head		straight
Sensing head thread		M6
Sensing head length	[mm]	45
Total length	[mm]	2000

E20524

Fibre optic diffuse reflection sensor

FT-00-M-V-M6/2m

Min. bending radius	[mm]	20
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		metal silicone
Remarks		
Pack quantity		1 pcs.