AC5200

AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4SB IP67



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	2; (AS-i: 2; AUX: 2)
Additional voltage supply	[V]	15...30 DC; (AUX ; "supply class 2" to cULus)
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
EMC		EN 50295
		IEC 61000-6-2
MTTF	[years]	10284
Mechanical data		
Weight	[g]	152.5
Type of mounting		AS-i flat cables directly connectable
Dimensions	[mm]	103 x 45 x 44.7
Materials		PA; piercing contacts: CuSn6 nickel-plated and tin-plated
Electrical connection		
Module connection		Flat cables
Accessories		
Items supplied		lower part

AC5200

AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4SB IP67

Accessories (optional)	Protective cap: M12, E73004

Remarks

Pack quantity	1 pcs.

Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Connector: M12; coding: A



1	AS-i +
2	external voltage -
3	AS-i -
4	external voltage +