DX2021

Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/AC/DC



panel cutout 91 x 43 mm

Product characteristics			
Dimensions	[mm]	48 x 112 x 116	
Application			
Application		universal evaluation and display for all physical units which can be derived from pulse sequences	
Electrical data			
Frequency AC	[Hz]	50...60	
Operating voltage	[V]	115...230 AC / 18...30 DC	
Current consumption	[mA]	100	
Inputs / outputs			
Number of inputs and outputs		Number of digital inputs: 2	
Inputs			
Number of digital inputs		2	
Operating conditions			
Ambient temperature	[°C]	-20...60	
Storage temperature	[°C]	-25...70	
Protection		IP 65	
Protection rating terminals		IP 20	
Tests / approvals			
EMC		EN 61000-6-2	
		EN 61000-6-3	
		EN 61000-6-4	
Mechanical data			
Weight	[g]	355	
Type of mounting		panel cutout: 91 x 43 mm	
Dimensions	[mm]	48 x 112 x 116	
Materials		Noryl UL94-V-0	
Displays / operating elements			
Display		colour display	full graphic LCD display, touch screen

DX2021

Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/AC/DC

Electrical connection

screw terminals:

Connection



NC: not used