# E12613

## Connection cable

ASTGH030MSS00,5H03




CE

| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Halogen-free |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 50 AC/DC |
| Protection class | | II |
| Max. current load total | [A] | 4 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...90 |
| Ambient temperature (moving) | [°C] | -25...90 |
| Protection | | IP 65 |
| **Mechanical data** | | |
| Weight | [g] | 30.5 |
| Materials | | housing: TPU orange; Lock nut: nickel-plated brass |
| Tightening torque | [Nm] | 0.6...1.5 |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |

# E12613

## Connection cable

ASTGH030MSS00,5H03

## Electrical connection

## Electrical connection

Cable: 0.5 m, PUR, Halogen-free, black, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm )

Connection




## Electrical connection