AC2386

AS-Interface illuminated pushbutton module

AS-i Module 2BI 2LO WT/WT



1 LED
2 pushbutton 2 / LED 2
3 pushbutton 1 / LED 1
4 panel for labelling

Application		
Design		Colour inserts changeable
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	55
Inputs		
Sensor supply of the inputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...85
Protection		IP 67
Tests / approvals		
EMC		EN 61000-6-2
		EN 62026-2
AS-i classification		
AS-i version		2.11; 3.0
Extended addressing mode		yes
AS-i master profile		M2; M3; M4

AC2386

AS-Interface illuminated pushbutton module

AS-i Module 2BI 2LO WT/WT

AS-i profile		S-7.A.E				
AS-i I/O configuration	[hex]	7				
AS-i ID code	[hex]	A.E				
AS-i certificate		133801				
Assignment of the data bits		data bit	D0	D1	D2	D3
		LED 1	DO-0	-	-	-
		LED 2	-	DO-1	-	-
		pushbutton 1	DI-0	-	-	-
		pushbutton 2	-	DI-1	-	-

Mechanical data

Weight	[g]	140	
Type of mounting		mounting on DIN rail	
Dimensions	[mm]	89.6 x 46 x 45	
Materials		PA	

Displays / operating elements

Display		operation	LED, green
		errors	LED, red
Operating elements		2	freely programmable backlit function keys

Electrical connection

Module connection	M12

Accessories

Items supplied	cover support: 2
	colour inserts: 2, red
	2, green
	2, yellow
	2, blue
	2, white

Remarks

Pack quantity	1 pcs.

Electrical connection



1	AS-i +
3	AS-i -