E10424

Connecting cable with socket

ADOAH042MSS0015A03

Article no longer available - archive entry



Electrical data			
Operating voltage	[V]	10...30 DC	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Protection		IP 67	
Mechanical data			
Dimensions	[mm]	27 x 15 x 39	
Materials		TPU transparent	
Moulded-body material		TPU, transparent	
Material nut		brass, nickel-plated	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

E10424

Connecting cable with socket

ADOAH042MSS0015A03

Electrical connection

Cable: 15 m, PUR / PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm

Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue