E11019

Splitter box

ZDO6H05DMSS0005H15

Article no longer available - archive entry

Alternative articles: EBC020

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	10...30 DC
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-15...80

E11019

Splitter box

ZDO6H05DMSS0005H15

Protection	IP 67	
Mechanical data		
Materials	TPU	
Moulded-body material	TPU	
Number of ports splitter box	6	
Connector type	M12	
Displays / operating elements		
Display	switching status	12 x LED, yellow
	operation	1 x LED, green
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Cable: 5 m, PUR, Halogen-free, black, Ø 10.4 mm; 12 x 0.5 mm² (63 x Ø 0.1 mm) + 3 x 1.0 mm² (127 x Ø 0.1 mm)

Electrical connection - slot

Connector: 6 x M12; coding: A; Moulded body: TPU; Contacts: gold-plated; Tightening torque: 0.5 Nm



E11019

Splitter box

ZDO6H05DMSS0005H15

Connection



	Core colours :
BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
RD =	red
WH =	white
YE =	yellow