E70454

AS-Interface flat cable insulation displacement connector

FC Splitter ye ProcessL

Article no longer available - archive entry

Alternative articles: E70455

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Design		AS-i
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Outputs		
Max. current load outputs total	[A]	2
Operating conditions		
Ambient temperature	[°C]	-30...80
Protection		IP 68; IP 69K
Tests / approvals		
EMC		EN 61000-6-2
Mechanical data		
Weight	[g]	49.5
Materials		metal parts: stainless steel (316L/1.4404); rubber gasket for contact pins: FPM; O-ring: EPDM
Accessories		
Accessories (optional)		Torque wrench:, E70390
Remarks		
Pack quantity		1 pcs.

E70454

AS-Interface flat cable insulation displacement connector

FC Splitter ye ProcessL

Electrical connection



Connection	
1	AS-i +
3	AS-i -

Electrical connection - socket

Connector: 1 x M12; Tightening torque: 0.6...0.8 Nm