E11502

Connecting cable with socket

ADOAF032VAS0010E03

Article no longer available - archive entry



Application			
Special feature		Free from silicone; Gold-plated contacts	
Free from silicone		yes	
Electrical data			
Operating voltage	[V]	10...30 DC	
Protection class		III	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...85	
Protection		IP 68	
Mechanical data			
Weight	[g]	312	
Dimensions	[mm]	18 x 10 x 28	
Materials		PVC	
Moulded-body material		PVC	
Material nut		stainless steel (316L/1.4404)	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

E11502

Connecting cable with socket

ADOAF032VAS0010E03

Electrical connection

Cable: 10 m, PVC, orange, Ø 5 mm; 3 x 0.25 mm² (32 x 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: PVC; Locking: stainless steel (316L/1.4404); Contacts: gold-plated; Tightening torque: 0.6...0.7 Nm



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue