E20240

Fibre optic diffuse reflection sensor

FT-30-A-A-R8/1M

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OIF
OIF		
Range fibre optics	[mm]	70
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		angled
Total length	[mm]	1000
Min. bending radius	[mm]	30
Materials		Adapter: PA
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		aluminium
Remarks		
Pack quantity		1 pcs.