E20215

Fibre optic diffuse reflection sensor

FT-00-M6

phase-out article



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF; OUF; OOF
OKF		
Range fibre optics	[mm]	40
OOF		
Range fibre optics	[mm]	200
OUF		
Range fibre optics	[mm]	40
Operating conditions		
Ambient temperature	[°C]	-25...80
Mechanical data		
Weight	[g]	20.7
Version of sensing head		straight; with adapter for direct mounting
Total length	[mm]	26
Fibre arrangement		◐
Fibre material		glass

E20215

Fibre optic diffuse reflection sensor

FT-00-M6

Fibre head material	stainless steel (303/1.4305)
Accessories	
Items supplied	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 2
	knurled nut: 1 x M11
Remarks	
Pack quantity	1 pcs.