E10486

Connecting cable with socket

ADOAH042MSS07,5F03

Article no longer available - archive entry



Electrical data			
Operating voltage	[V]	10...30 DC	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Protection		IP 67	
Mechanical data			
Dimensions	[mm]	27 x 15 x 39	
Materials		TPU transparent	
Moulded-body material		TPU, transparent	
Material nut		brass, anti-spatter	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

E10486

Connecting cable with socket

ADOAH042MSS07,5F03

Electrical connection

Cable: 7.5 m, PVC, orange, Ø 5 mm; cross-linked; 3 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, anti-spatter

Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue