E20199

Fibre optic diffuse reflection sensor

FT-00-R3



1 Lock nut
2 OKF with fibre optics

Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF
OKF		
Range fibre optics	[mm]	25
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Weight	[g]	14.5
Version of sensing head		angled; with adapter for direct mounting
Total length	[mm]	24
Fibre arrangement		◐
Materials		Lock nut: plastics
Fibre material		glass
Fibre head material		stainless steel (303/1.4305)
Remarks		
Pack quantity		1 pcs.