E33021

Process adapter Varivent

ADAP IFM-VARIV D=50(DN25/1)

Article no longer available - archive entry

Alternative articles: E33721

When selecting an alternative article and accessories please note that technical data may differ!

The alternative article requires the use of a new sensor with Aseptoflex Vario external thread



1 Aseptoflex thread
2 Aseptoflex sealing edge

EC 1935/2004 EHEDG Certified FDA

Application		
Pressure rating	[bar]	25
Tests / approvals		
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions		The compatibility between medium and product material has to be checked in all applications.
Mechanical data		
Weight	[g]	241.8
Materials		stainless steel (1.4404 / 316L)
Sensor connection		Aseptoflex
Process connection		Varivent Form F, DN25 (1"), Ø 50 mm
Surface characteristics Ra/Rz of the wetted parts		0.4 / 4
Hygienic equipment class to DIN 11866		H4
Remarks		
Pack quantity		1 pcs.