E38826

Thermowell for temperature sensors

THERMOWELL, D3/DN25 Ingold/EL=25



1 retaining ring
2 Lock nut G 1 1/4
3 O-ring

Application		
Design		for temperature sensors EL = 83 mm
Pressure rating	[bar]	16
Mechanical data		
Weight	[g]	868
Materials		stainless steel (316L/1.4435)
Sensor connection		G 3/8 internal thread Ø 3 mm
Process connection		Ingold Ø 25 mm
Surface characteristics Ra/Rz of the wetted parts		< 0.4 / -
Installation length EL	[mm]	25
Bore length BL	[mm]	83
Remarks		
Pack quantity		1 pcs.