E3M120

Connection cable

MCI CONNECTION CABLE 0.25M



Application			
Special feature			Drag chain suitability
Electrical data			
Operating voltage	[V]		< 25 AC / < 60 DC
Operating conditions			
Ambient temperature	[°C]		-40...105
Protection			IP 67
Mechanical data			
Weight	[g]		39.55
Drag chain suitability			yes
Drag chain suitability		bending radius for fixed installation	≥ 40 mm
Remarks			
Pack quantity			1 pcs.
Electrical connection			
Cable: 0.25 m, TPU, black			