E11090

Connecting cable with socket

ADOAF030VAS0010E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	17 x 10 x 26
Materials		TPU
Moulded-body material		TPU
Material nut		stainless steel (303/1.4305)
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 10 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU; Locking: stainless steel (303/1.4305)



E11090

Connecting cable with socket

ADOAF030VAS0010E03

Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue