E20138

Fibre optic diffuse reflection sensor

FT-00-A-A-E3/2M

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF; OUF
OKF		
Range fibre optics	[mm]	32
OUF		
Range fibre optics	[mm]	32
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		straight
Sensing head diameter	[mm]	3
Sensing head length	[mm]	10
Total length	[mm]	2000
Min. bending radius	[mm]	20
Materials		Adapter: ABS
Fibre material		glass

E20138

Fibre optic diffuse reflection sensor

FT-00-A-A-E3/2M

Fibre head material	aluminium
Fibre sheath material	aluminium

Remarks	
Pack quantity	1 pcs.