AC2307

AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T6 2SI 2DO T M12

Article no longer available - archive entry

Alternative articles: AC2317
When selecting an alternative article and accessories please note that technical data may differ!



1 sensor 1
2 sensor 2

Product characteristics		
Sensing range	[mm]	4
Dimensions	[mm]	55 x 60 x 35
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Detection zone		
Sensing range	[mm]	4
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 67

AC2307

AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T6 2SI 2DO T M12

Tests / approvals			
EMC		EN 50081-1	
		EN 61000-6-2	

AS-i classification		
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	F
AS-i certificate		15101

Mechanical data		
Mounting		non-flush mountable
Dimensions	[mm]	55 x 60 x 35
Materials		PBT; PC

Displays / operating elements		
Display	operation	1 x LED, green
	function	1 x LED, red

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Moulded body: stainless steel



Elektrischer Anschluss	
1	AS-i+
3	AS-i -

Electrical connection - socket

Connector: 1 x M12; coding: A; Moulded body: stainless steel



Connection	

Ausgänge	
2	switching output 2 +
3	external voltage -
4	switching output 1 +