AC5022

Lower part for AS-Interface module

EMS-Base FC Address.socket

Article no longer available - archive entry



1 earthing lead
2 addressing socket

Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Additional voltage supply	[V]	24 DC
Outputs		
Electrical design		AS-i
Contact rating		< 2 A
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67; (depending on the upper part used: IP 20 / IP 65 / IP 67)
AS-i classification		
AS-i addressing		addressing socket
Mechanical data		
Type of mounting		mounting on DIN rail and panel
Dimensions	[mm]	45 x 80 x 20
Materials		PBT
Remarks		
Remarks		recommended sleeve for earthing lead: A 2.8 x 0.5 DIN 46247
		Module lower part can be used with upper parts where pin 5 of the M12 socket is connected to functional earth (FE).
Pack quantity		1 pcs.
Electrical connection		

contact pins in module upper part :

AC5022

Lower part for AS-Interface module

EMS-Base FC Address.socket

quick mounting technology for AS-i flat cable: