E18129

Connecting cable with socket

ADOAH040VAS0060E04



Application		
Special feature		Gold-plated contacts
Electrical data		
Operating voltage	[V]	< 300 AC/DC
Operating conditions		
Ambient temperature	[°C]	-20...105
Protection		IP 68
Mechanical data		
Weight	[g]	2100.131
Dimensions	[mm]	31 x 14.5 x 31
Materials		PVC
Moulded-body material		PVC
Material nut		stainless steel (316Ti/1.4571)
Remarks		
Pack quantity		1 pcs.

E18129

Connecting cable with socket

ADOAH040VAS0060E04

Electrical connection

Cable: 60 m, PVC, grey; 4 x 0.34 mm² / AWG 22

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PVC; Locking: stainless steel (316Ti/1.4571); Contacts: gold-plated



Connection



5:	not used
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white