# KI5060

## Capacitive sensor

KI-2015-FRKG/NI/PH

Article no longer available - archive entry

Alternative articles: KI5082

When selecting an alternative article and accessories please note that technical data may differ!




| | | |
|---|---|---|
| **Product characteristics** | | |
| Electrical design | | PNP/NPN |
| Output function | | normally open / normally closed; (selectable) |
| Sensing range | [mm] | 3...15 |
| Housing | | threaded type |
| Dimensions | [mm] | M30 x 1.5 / L = 81 |
| **Electrical data** | | |
| Operating voltage | [V] | 10...36 DC |
| Protection class | | II |
| Reverse polarity protection | | yes |
| **Outputs** | | |
| Electrical design | | PNP/NPN |
| Output function | | normally open / normally closed; (selectable) |
| Max. voltage drop switching output DC | [V] | 4.6 |
| Minimum load current | [mA] | 5 |
| Max. leakage current | [mA] | 1 |
| Permanent current rating of switching output DC | [mA] | 250 |
| Switching frequency DC | [Hz] | 40 |
| Short-circuit proof | | yes |
| Overload protection | | yes |
| **Detection zone** | | |
| Sensing range | [mm] | 3...15 |
| Sensing range adjustable | | yes |
| Factory setting sensing range | [mm] | 15 |
| Real sensing range Sr | [mm] | 15 ± 10 % |
| Operating distance | [mm] | 0...12.1 |

# KI5060

## Capacitive sensor

KI-2015-FRKG/NI/PH

| | | | |
|---|---|---|---|
| **Accuracy / deviations** | | | |
| Correction factor | | glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2 | |
| Hysteresis | [% of Sr] | 1...15 | |
| Switch point drift | [% of Sr] | -15...15 | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | -25...80 | |
| Protection | | IP 65 | |
| **Tests / approvals** | | | |
| EMC | | EN 60947-5-2 | |
| **Mechanical data** | | | |
| Weight | [g] | 193.8 | |
| Housing | | threaded type | |
| Mounting | | non-flush mountable | |
| Dimensions | [mm] | M30 x 1.5 / L = 81 | |
| Thread designation | | M30 x 1.5 | |
| Materials | | PBT | |
| **Displays / operating elements** | | | |
| Display | | switching status | 1 x LED, yellow |
| **Accessories** | | | |
| Items supplied | | lock nuts: 2 | |
| | | screwdriver: 1 | |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |
| **Electrical connection** | | | |

Cable: 2 m, PUR / PVC; 2 x 0.5 mm²

Connection







Core colours :
BK = black
WH = white