E10095

Wirable socket

SDOAH042ZDSFKPG

Article no longer available - archive entry

Alternative articles: E11510

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data			
Operating voltage	[V]		10...30 DC
Outputs			
Electrical design			NPN
Operating conditions			
Ambient temperature	[°C]		-25...90
Protection			IP 67
Mechanical data			
Dimensions	[mm]		36 x 20 x 31
Materials			PA
Moulded-body material			PA
Material nut			diecast zinc, nickel-plated
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10095

Wirable socket

SDOAH042ZDSFKPG

Electrical connection

terminals: ...0.75 mm²; Cable gland: PG 7

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PA; Locking: diecast zinc, nickel-plated

Connection