E10611

Connecting cable with socket

ADOAH042VAS0020E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...30 DC
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Materials		PUR
Moulded-body material		PUR
Material nut		stainless steel (303/1.4305)
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 20 m, PVC, black, Ø 4.5 mm; 3 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: stainless steel (303/1.4305)

E10611

Connecting cable with socket

ADOAH042VAS0020E03

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue