E10863

Connecting cable with socket

ADOAF040MSS0002A04

Article no longer available - archive entry

Alternative articles: E11199

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67; (if screwed on)
Mechanical data		
Dimensions	[mm]	16 x 8 x 26
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 2 m, PUR / PVC, orange, Ø 5 mm; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

E10863

Connecting cable with socket

ADOAF040MSS0002A04

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white