E10274

Connecting cable with socket

ADOAF032MSS0002A03

Article no longer available - archive entry

Electrical data			
Operating voltage	[V]		10...30 DC
Protection class			III
Outputs			
Electrical design			PNP
Operating conditions			
Ambient temperature	[°C]		-25...90
Protection			IP 67
Mechanical data			
Dimensions	[mm]		17 x 10 x 26
Materials			TPU transparent
Moulded-body material			TPU, transparent
Material nut			brass, nickel-plated
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10274

Connecting cable with socket

ADOAF032MSS0002A03

Electrical connection

Cable: 2 m, PUR / PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, nickel-plated



Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue