E11318

Connection cable

VDOGF030MSS0005B03STGF030MSS

Article no longer available - archive entry

Alternative articles: E11353

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	10...30 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68
Mechanical data		
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.6...0.7 Nm

E11318

Connection cable

VDOGF030MSS0005B03STGF030MSS

Electrical connection

Cable: 5 m, TPU, black, Ø 4.5 mm; 3 x 0.25 mm² (32 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.6...0.7 Nm