E18267

CAN bus terminating resistor

M12 PASSTHROUGH W/RESISTOR



Application		
Special feature		Gold-plated contacts
Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-40...85
Protection		IP 68
Mechanical data		
Weight	[g]	22.68
Dimensions	[mm]	14.5 x 14.5 x 52.8
Materials		PVC
Moulded-body material		PVC
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: brass, nickel-plated; Contacts: gold-plated



E18267

CAN bus terminating resistor

M12 PASSTHROUGH W/RESISTOR

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: brass, nickel-plated; Contacts: gold-plated



Connection