# E10518

## Connecting cable with socket

ADOAH042MSS0005F03

Article no longer available - archive entry




| | | | |
|---|---|---|---|
| **Electrical data** | | | |
| Operating voltage | [V] | 10...30 DC | |
| **Outputs** | | | |
| Electrical design | | PNP | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | -25...90 | |
| Protection | | IP 67 | |
| **Mechanical data** | | | |
| Dimensions | [mm] | 27 x 15 x 39 | |
| Materials | | TPU transparent | |
| Moulded-body material | | TPU, transparent | |
| Material nut | | brass, anti-spatter | |
| **Displays / operating elements** | | | |
| Display | | switching status | 1 x LED, yellow |
| | | operation | 1 x LED, green |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |

# E10518

## Connecting cable with socket

**ADOAH042MSS0005F03**

### Electrical connection

Cable: 5 m, PVC, orange, Ø 5 mm; cross-linked; 3 x 0.34 mm²

### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, anti-spatter

### Connection




| | Core colours : |
|---|---|
| BN = | brown |
| BK = | black |
| BU = | blue |