# E11266

## Connection cable

VDOAH040MSS0002H03STGF030MSS

Article no longer available - archive entry




| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Halogen-free; Gold-plated contacts |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 60 AC / < 75 DC |
| Protection class | | III |
| Max. current load total | [A] | 3 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...85 |
| Protection | | IP 68 |
| **Mechanical data** | | |
| Materials | | PUR |
| Moulded-body material | | PUR |
| Material nut | | brass, nickel-plated |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |

# E11266

## Connection cable

VDOAH040MSS0002H03STGF030MSS

### Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...0.7 Nm




### Electrical connection

Cable: 2 m, PUR, Halogen-free, black, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm )

Connection




### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm