E2M251

Connection cable for E2M250 multi-view box

CONNECTION CABLE M16 8P 3,85M



Application		
Special feature		Halogen-free; Drag chain suitability
Design		For connection of the MultiViewBox E2M250
Electrical data		
Operating voltage	[V]	< 60 DC
Operating conditions		
Ambient temperature	[°C]	-45...85
Protection		IP 67
Mechanical data		
Weight	[g]	322.8
Materials		housing: diecast zinc; Sealing: PBT
Material nut		diecast zinc
Drag chain suitability		yes
Drag chain suitability		bending radius for fixed installation ≥ 100 mm
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 3.85 m, PUR, Halogen-free, black, Ø 6 mm; 7 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M16, straight; coding: A; Locking: diecast zinc

1	12 / 24 V DC red
2	GND white
3	IN 1 blue
4	IN 2 brown
5	IN 3 white/yellow
6	IN 4 grey
7	not used
8	not used