AC2350

AS-Interface illuminated pushbutton module

Push-button modul 8I/8O

Article no longer available - archive entry

Alternative articles: AC2351

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 150
Reverse polarity protection		yes
Outputs		
Electrical design		AS-i
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 00
Tests / approvals		
EMC		EN 50295

AC2350

AS-Interface illuminated pushbutton module

Push-button modul 8I/8O

AS-i classification		
AS-i profile		S-7.F
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	F
AS-i certificate		14401
Mechanical data		
Materials		front panel: aluminium
Accessories		
Accessories (optional)		Cover removal tool:, E70206
Remarks		
Remarks		The pushbuttons (EAO type 84) provide protection against accidental contact.
		Housing and pushbuttons can be labelled.
Pack quantity		1 pcs.
Electrical connection		
COMBICON:		