E10870

Connecting cable with socket

ADOAH043MSS0005H04

Article no longer available - archive entry



Application			
Special feature		Halogen-free	
Electrical data			
Operating voltage	[V]	10...30 DC	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Protection		IP 67	
Mechanical data			
Dimensions	[mm]	27 x 15 x 39	
Materials		TPU	
Moulded-body material		TPU	
Material nut		brass, anti-spatter	
Displays / operating elements			
Display		switching status	2 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

E10870

Connecting cable with socket

ADOAH043MSS0005H04

Electrical connection

Cable: 5 m, PUR, Halogen-free; cross-linked; 4 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, anti-spatter

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white