AC2027

AS-Interface AirBox

AirBox 2DI 2PO M12



1 tube connection Ø 8 mm
2 panel for labelling

Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	150
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of pneumatic outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Power supply	[V]	20...30
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	> 3
Input current Low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits		yes
Outputs		
Number of pneumatic outputs		2

AC2027

AS-Interface AirBox

AirBox 2DI 2PO M12

Actuator supply outputs		AS-i				
Operating conditions						
Ambient temperature	[°C]	0...55				
Note on ambient temperature		with special compressed air treatment: < 0 °C				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
AS-i classification						
Extended addressing mode		no				
AS-i profile		S-3.F				
AS-i I/O configuration	[hex]	3				
AS-i ID code	[hex]	F				
AS-i certificate		10501				
Assignment of the data bits		data bit	D0	D1	D2	D3
		Inputs / outputs	I-1	I-2	O-3	O-4
Mechanical data						
Weight	[g]	254.5				
Type of mounting		screw mounting				
Materials		PBT				
Pneumatic system		2 x 3/2-way seat valves				
Operating pressure range	[bar]	2...8				
Operating pressure range	[MPa]	0.2...0.8				
Note on working pressure range		incl. possible pressure peaks				
Air flow at 6/5 bar	[l/min]	350				
Air flow at 6/0 bar	[l/min]	550				
Permissible compressed air		filtered (5 µm); lubricated (ISO-VG10) or not lubricated				
Tube fittings		Legris LF 3000/8				
Exhaust		exhaust can be discharged through tube connection				
Displays / operating elements						
Display		operation	LED, green			
		function	LED, yellow			
Electrical connection						
Module connection		Flat cables				
Accessories						
Accessories (optional)		silencer:, E75232				
Remarks						
Remarks		Please see the notes on compressed air and EMC/ESD under "Downloads"				
Pack quantity		1 pcs.				

AC2027

AS-Interface AirBox

AirBox 2DI 2PO M12

Electrical connection

contact pins to module lower part, FK / PG:

Connector: M12; coding: A



	Inputs
1	Sensor supply L+
2+4	data input internally bridged
3	Sensor supply L-