E10931

Connection cable

VDOAF032MSS00,6H03STGF030MSS

Article no longer available - archive entry

Alternative articles: E11330
When selecting an alternative article and accessories please note that technical data may differ!



Application			
Special feature			Halogen-free
Electrical data			
Operating voltage	[V]		10...30 DC
Protection class			III
Operating conditions			
Ambient temperature	[°C]		-25...90
Protection			IP 67
Mechanical data			
Materials			TPU
Moulded-body material			TPU
Material nut			brass, nickel-plated
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10931

Connection cable

VDOAF032MSS00,6H03STGF030MSS

Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

Electrical connection

Cable: 0.6 m, TPU, Halogen-free; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated