E10158

Connecting cable with socket

ADOAH042MSS0002E03

Article no longer available - archive entry

Alternative articles: EVC615

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data			
Operating voltage	[V]		10...30 DC
Outputs			
Electrical design			PNP
Operating conditions			
Ambient temperature	[°C]		-25...80
Protection			IP 67
Mechanical data			
Weight	[g]		65.4
Dimensions	[mm]		26 x 15 x 38
Materials			TPU transparent
Moulded-body material			TPU, transparent
Material nut			brass, nickel-plated
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity			1 pcs.

E10158

Connecting cable with socket

ADOAH042MSS0002E03

Electrical connection

Cable: 2 m, PUR, black, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm

Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue