E19938

Splitter box



Electrical data		
Operating voltage	[V]	10...110 AC/DC
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12
Operating conditions		
Ambient temperature	[°C]	-15...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	16 x 54 x 127
Number of ports splitter box		8
Remarks		
Pack quantity		1 pcs.

E19938

Splitter box

Electrical connection

Cable: 5 m, PUR / PVC; 8 x 0.34 mm² + 3 x 0.75 mm²

Electrical connection - slot

Connector: 8 x M12; coding: A



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GN =	green
GN/YE =	green/yellow
GY =	grey
PK =	pink
RD =	red
VT =	lilac
WH =	white
YE =	yellow